



Layouts

ingenio gravio 90200

Layouts for all demands

Our ingenio lab presses give you the opportunity to test your inks and materials extensively in order to determine the best printing parameters before commercial production. This gives you a high degree of flexibility and control over the final appearance of your print product.

To ensure that the results on the ingenio meet your requirements, we offer a wide portfolio of different cylinder specifications and gradations and advise you on their selection. Choose the right layout for your application from our layout brochure or let our experts create your individual layout. There are no limits to creativity: solid areas, color wedges, color gradients, lines in different thicknesses, logos, patterns or texts - the choice of possible layout elements is limitless.

Feel free to contact us!




Layout G

Layout G consists of:

- two solid areas
- one color gradation (100 % - 5 %)
- one color gradation (5 % - 100 %)
- one gradient (0 % - 100 %)
- one gradient (100 % - 0 %)


cylinder circumference: 282.743 mm
cylinder width: 200.00 mm
printing width: 170.00 mm



Layout H

- Layout H consists of:
- five adjacent solid areas


cylinder circumference: 282.743 mm
cylinder width: 200.00 mm
printing width: 170.00 mm



Layout I


- Layout I consists of:
- a large solid area

cylinder circumference: 282.743 mm
cylinder width: 200.00 mm
printing width: 170.00 mm



Layout J


- Layout J consists of:
- different solid areas
 - different color gradations (100 % - 5 %)
 - different color gradients (0 % - 100%)
- cylinder circumference: 282.743 mm
cylinder width: 200.00 mm
printing width: 170.00 mm



Single image Layout J


Remark:
Layouts J and K are available as a combination layout.

Layout K



Single image Layout K

- Layout K consists of:
- different solid areas
 - different color gradations (100% - 5 %)
 - different color gradients (0% - 100%)
- cylinder circumference: 282.743 mm
cylinder width: 200.00 mm
printing width: 170.00 mm




Layout L

Layout L consists of six equal representations with each:

- one solid area
- a color gradation (100 % - 0 %)
- a gradient (100 % - 0 %)

cylinder circumference: 282.743 mm
cylinder width: 200.00 mm
printing width: 170.00 mm




Layout M

Layout M consists of four equal representations with each:

- one solid area
- a color gradation (100 % - 5 %)
- a gradient (100 % - 0 %)


cylinder circumference: 282.743 mm
cylinder width: 200.00 mm
printing width: 170.00 mm



Layout N

- Layout N consists of:
- four solid areas for different specifications/colors
 - four color gradations (100 % - 5 %)

cylinder circumference: 282.743 mm
cylinder width: 200.00 mm
printing width: 170.00 mm




Layout ○

Layout O consists of:

- Solid areas
- Color gradation 100 % - 5 %
- Text boxes positive and negative
- Different shapes and line widths

cylinder circumference: 282.743 mm
cylinder width: 200.00 mm
printing width: 170.00 mm



EN



Matthews International GmbH
Gutenbergstraße 1-3
48691 Vreden | Germany
T: +49 2564 229

e.GEN@saueressig.com
saueressig.com

Follow SAUERESSIG Group



Matthews
INTERNATIONAL®

SAUERESSIG Group and SAUERESSIG e.GEN are
(MATW) Matthews International brands.

